

HIGH PERFORMANCE LED FLOODLIGHTS

LED security floodlight

*Delivering the promise of LED
Industry-leading performance and value.
Unmatched cost-per-lumen solution
for outdoor security lighting.*



LED Floodlights from Lithonia Lighting® integrate long-life LED technology in an affordable, energy-saving security lighting solution.

- Uses 78% less energy than a standard incandescent lamp solution
- 50,000-hour maintenance free
- Bright, uniform illumination for safety and security
- Integrated motion sensor and dusk-to-dawn photocell available
- Tool-free adjustable heads for optimal light distribution
- Rugged, cast-aluminum, corrosion-resistant housing
- Clear acrylic lenses are fully gasketed to keep out moisture, dirt and bugs
- Quality tested in accordance with IESNA LM-79 and LM-80

Ideal for residential and light commercial applications.

**50,000
HOURS
LIFE**

Maintenance
FREE



3-HEAD

\$961
avg. savings
over life*

1636
lumens

2-HEAD

\$645
avg. savings
over life*

1096
lumens

- Motion detector with sensitivity and on-time adjustable knobs for precision control.
- Adjustable motion sensor up to 180° range and 70 feet with downward perimeter protection.
- Motion sensor manual override.
- Bronze finish.

Red Book

6ECJ1 - 3 Light Motion Sensor

6ECJ3 - 2 Light Motion Sensor

*savings based on operating 12hrs/day, 365 days/year at .12 kwh

**SAVE MONEY
&
STAY SAFE**

Dusk-to-Dawn

3-HEAD

\$1012
avg. savings
over life*

1719
lumens

2-HEAD

\$720
avg. savings
over life*

1222
lumens

- Photocell automatically turns light on at dusk and off at dawn for security, convenience and energy savings.
- Bronze finish.

Red Book

6ECJ2 - 3 Light Dusk-to-Dawn

6ECJ4 - 2 Light Dusk-to-Dawn



OLW™

OUTDOOR LED WALL PACK

*Value and versatility defined.
The OLW14 makes the switch to
LED easy and affordable!*

Red Book # 6MGH3

**1436
lumens
LED**

The OLW14 LED wall pack from Lithonia Lighting® delivers the promise of LED in a contemporary, lightweight design. Its superior optics provide bright, even illumination - delivering the light exactly where you need it.

- The OLW14 LED wall pack at a glance:
- High-performance LED technology
- Adjustable MVOLT photocell, standard
- MVOLT driver for 120-277V
- 6kV surge protection, standard
- 50,000 hours maintenance free
- Nighttime Friendly™ full cutoff with optional shield
- Tested in accordance with IESNA LM-79 and LM-80
- Rugged, die-cast aluminum housing
- Junction box for surface- or recess-mounting options
- Lightweight, compact size



\$1235
avg. savings
per fixture vs
100W
incandescent*

\$293
avg. savings
per fixture vs
42 TRT CFL*

\$380
avg. savings
per fixture vs
50W
metal halide*

\$319
avg. savings
per fixture vs
50W HPS*

*Energy savings based on difference in input watts @ \$0.12KWh and includes 15 minutes of labor and replacement lamp costs.

Versatile Application:



Industrial



Multi-unit / Education



Retail / Commercial

Value and versatility defined



www.lithonia.com/OLW



For more information, contact your Grainger Seller.

© 2011 Acuity Brands Lighting, Inc.
02/11 CP7243 Form No. 522.41



AVAILABLE THROUGH

GRAINGER
FOR THE ONES WHO GET IT DONE