



# Critical Area Vacuums

## Backpack Vacuums



### GD 10 Back

The GD10 Back Vacuum was designed with comfort and ease-of-use in mind. For its small size, the GD10 Back is incredibly powerful and equipped with a variety of features for fast, effective cleaning in a multitude of industries. In 2008, it was awarded a Green Label Seal of Approval by the Carpet and Rug Institute.

Amps	Static Pressure (in.)	CFM @ 2"	Motor Type	Cord Length (ft.)	Item No.
9.5	99	144	1-stage	50	4NFP4



### UZ 964 Hip Vac

The revolutionary UZ 964 Hip Vac is a compact, ergonomic vacuum cleaner that delivers superior productivity. Designed for operator comfort, the vacuum sits on the user's lower back, allowing freedom of movement and reducing back strain.

Amps	Static Pressure (in.)	CFM @ 2"	Motor Type	Cord Length (ft.)	Item No.
6.0	76	59	1-stage	50	4NFP6

## Mercury Recovery Vacuums



### SS Mercury and VT Mercury

Activated carbon absorbent filter prevents mercury from escaping into exhaust air. Safety latches provide added security. VT model includes a microstatic diffuser to protect the motor and a separator to collect liquid mercury.

	Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (in.)	Tank Type	Item No.
SS Mercury	2.2	1.5	9	87	102	Stainless Steel	4NFT8
VT Mercury	12	1.3	8.3	99	117	Polyethylene	4NFT5

# Dry Vacuums



## GM 80 / GM 80CR

Lightweight and portable, the GM 80 is a versatile machine that provides durability and performance. It features a standard multi-stage filtration system with a paper dust bag, main filter, microfilter and HEPA exhaust filter.

The GM 80CR is lightweight, portable and quiet-- perfect for cleanrooms, research labs, and other critical environments. A four-stage filtration system comes standard with an ULPA exhaust filter.

	Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (in.)	Tank Type	Item No.
GM 80	3.25	1.5	9	87	102	Aluminum	4RXY7
GM 80CR	3.25	1.5	9	87	102	Aluminum	4NFP9



## IVT 1000CR / Safe-Pak

The IVT 1000CR vacuum features everything customers asked for...and more. From multi-stage filtration to the standard stainless steel design to the quiet 61 dB(A) noise level, the next level of cleanroom vacuum is here. This vacuum is also available with the Nilfisk Safe-Pak container for safe collection, containment and disposal of potent compounds.

	Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (in.)	Tank Type	Item No.
IVT 1000CR w/ Safe-Pak	3.25	1.5	9	72	80	Stainless Steel	4RXY8
IVT1000CR	3.25	1.5	9	76	79	Stainless Steel	4RXY9



## Eliminator I

The Eliminator I features a 3-stage filtration system for dry collection and an easy to empty 5-gallon collection container. Operates at 59 dB(A).

Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (in.)	Tank Type	Item No.
5	1.8	11.2	130	95	Polypropylene	4NFT3

## Wet/Dry Vacuums



### Eliminator I WD and Eliminator II

Features a 3-stage filtration system, wheeled trolley, and a large ergonomic handle for easy transport. A float valve shuts unit off when container is full.

	Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (In.)	Tank Type	Item No.
Eliminator I WD	5	1.8	11.2	130	95	Polypropylene	4NFR7
Eliminator II	12	1.8	11.2	130	95	Polypropylene	4NFT1



### GWD 120 and GWD 220

The GWD 120 single-motor and the GWD 220 double-motor are wet/dry vacuums equipped with a 20-gallon stainless steel collection container. Both models feature float baskets and filters that are easy to access for cleaning and maintenance. Easy "tip-and-pour" system allows for easy disposal of liquids.

	Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (In.)	Tank Type	Item No.
GWD 120	20	1.8	11.2	89	88	Stainless Steel	4RXY5
GWD 220	20	2.4	12	220	80	Stainless Steel	4RXY6



### GWD 255

Powered by 2 independent bypass motors, this drum-top vacuum can fit both 30- and 55-gallon drums. Washable main sack filter helps extend filter life.

Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (In.)	Tank Type	Item No.
-	2.4	12	220	80	Painted Metal	4NFU1

# Explosion-Proof Vacuums



## 118 EXP and 118 EXP W

Made of 304 stainless steel and sold with conductive accessories, these explosion-proof vacuums are CSA-approved for use in Class I, Group D, and Class II, Groups E, F & G environments. The 118 EXP is for dry applications, while the 118 EXP W is for liquid collection.

	Tank Size (gal.)	HP	Amps @ 120V	CFM @ 2"	Static Pressure (in.)	Tank Type	Item No.
118 EXP	6.6	1.3	10	130	69	Stainless Steel	4NFR2
118 EXP W	13.2	1.3	10	130	69	Stainless Steel	4NFR5

## Tool Kits

**No. 4RXZ2 Wet/Dry Vac Kit (Eliminator I, Eliminator II, GWD 120, GWD 220)** — Includes hose assembly, floor nozzle with 3 inserts, crevice nozzle, dust brush, and 2 telescoping wands.

**No. 4RXZ7 Drum Top Vac Kit, 50mm** — Includes inlet reducer, vinyl hose cuff, wand, floor nozzle, brush strip, crevice nozzle, dust brush, and hose coupler.

**No. 4RXZ6 Drum Top Vac Kit, 38mm** — Includes inlet coupler, hose, hose handle, hose cuff, 2 wands, floor nozzle with 3 inserts, crevice device, and dust brush.

**No. 4RXZ8 Dry-Only Vac Kit (GM 80CR)** — Includes hose assembly, 2 wands, floor nozzle, crevice nozzle, dust brush, and utility tool.

**No. 4RXZ3 Explosion-proof Dry Vac Kit (118 EXP)** — Includes hose assembly, hose coupler, floor nozzle, crevice nozzle, dust brush, hose clamp, and 2-piece wand.

**No. 4RXZ4 Explosion-proof Wet/Dry Vac Kit** — Includes hose assembly, hose coupler, floor nozzle, floor squeegee, crevice nozzle, dust brush, hose clamp, and 2-piece wand.

**No. 4RXZ9 Mercury Hose Kit (SS Mercury)** — Includes hose assembly.

**No. 4RXZ5 Mercury Tool Kit (VT Mercury)** — Includes hose assembly and crevice nozzle.

**No. 4RYA2 Dry-Only Vac Kit (GM 80)** — Includes hose assembly, 2 wands, combination floor nozzle, dust brush, crevice nozzle, and upholstery tool.

**No. 4RYA3 ULPA Filter Dry Vac Kit (IVT 1000CR)** — Includes 2 wands, stainless steel curved tube, floor nozzle, hose, cuff, crevice nozzle, dust brush, and cap plug.

**A Spotless Reputation...  
With a Guarantee to Prove It**

We've earned our solid reputation by consistently producing top-quality vacuums and offering the industry's most complete selection of vacuum filtration options, attachments and accessories.

We back all of our products with our industry-leading two-year warranty. Nilfisk empowers you with complete buying confidence.

**Nilfisk-Advance America, Inc.**  
300 Technology Drive • Malvern, PA 19355-1315  
Phone: 610-647-6420 • Fax: 610-647-6427  
Toll-Free: 800-NILFISK (645-3475)  
E-mail: [questions@nilfisk-advance.com](mailto:questions@nilfisk-advance.com)  
Web: [www.nilfiskcfm.com](http://www.nilfiskcfm.com)

AVAILABLE THROUGH

**GRAINGER**  
