

Low Profile and Insulated Ceiling Ventilators

Horizontal mount ceiling fans exhaust air in bathrooms, meeting rooms, utility rooms, and offices. Single-speed motors have thermal overload protection and are compatible for use with adjustable speed controls. Galvanized steel housing and attractive white grille with concealed attachment screws for rattle-free operation. Includes electrical junction box, disconnect, and adjustable mounting brackets.

A Tradition of Performance, Reliability and Value.

Low Profile Ventilators

Compact size for height-restricted areas. Feature aluminum backdraft damper, round standard outlet, electrical access and junction box, disconnect and adjustable mounting brackets.

Insulated Ventilators

Acoustic insulation absorbs sound for quiet operation. Exhaust outlets are field rotatable from horizontal to vertical discharge. Spring loaded aluminum backdraft damper eliminates rattling. External electrical access reduces installation time. Horizontal and vertical electrical knockout points eliminate drilling holes.

5AE70

Insulated ceiling ventilator. Galvanized housing for use with general ventilation applications.



Dayton products are available at Grainger.

There are many ways to get the Dayton products you need — phone, fax, online at grainger.com/dayton or stop by your local Grainger® branch.

Low Profile and Insulated Ceiling Ventilators

- UL Listed for above bathtub/shower when connected to a GFCI branch-protected circuit
- Removable power assembly
- Attractive oversized white plastic grille

LOW PROFILE AND INSULATED VENTILATORS

CFM @ STATIC PRESSURE SHOWN							SOUND @ 0.100" SP SONES	VOLTAGE	RPM	WATTS	AMPS	STOCK NO.
0.100" SP	0.125" SP	0.250" SP	0.375" SP	0.500" SP	0.625" SP	0.750" SP						
92	88	75	59	45	30	—	2.6	115	700	50	0.65	5AE68
156	155	154	152	149	147	138	3.3	115	1050	129	1.70	5AE69
110	106	88	—	—	—	—	1.2	115	950	49	0.58	5AE70
197	192	167	133	—	—	—	2.8	115	1400	113	1.30	5AE71
225	220	196	172	142	105	67	2.3	115	900	48	0.43	5AE72
293	287	257	231	207	175	124	3.3	115	1050	81	0.72	5AE73
395	391	368	345	325	307	279	5.4	115	1350	135	1.34	5AE74
512	501	439	392	325	—	—	5.7	115	1070	224	3.30	5AE75
729	723	700	679	649	613	560	6.1	115	1100	350	3.20	5AE76
782	775	741	704	665	625	581	10.2	115	1600	348	3.30	5AE77
907	896	841	773	701	—	—	5.7	115	950	285	4.00	5AE78
1059	1043	964	885	796	662	—	7.0	115	1095	420	6.30	5AE79
1414	1404	1353	1307	1262	1218	1174	11.6	115	1450	786	7.40	5AE80
1568	1558	1506	1449	1407	1369	1323	12.1	115	1610	818	8.60	5AE81

LOW PROFILE VENTILATORS

HOUSING DIMENSIONS (IN.)			DISCHARGE DIMENSIONS	RECOMMENDED SPEED CONTROL	STOCK NO.
H	L	W			
7 15/16	13 7/8	11 1/2	6" Diameter	4YC44	5AE68
7 15/16	13 7/8	11 1/2	6" Diameter	4YC44	5AE69

INSULATED VENTILATORS

HOUSING DIMENSIONS (IN.)			DISCHARGE DIMENSIONS (IN.)		RECOMMENDED SPEED CONTROL	STOCK NO.
H	L	W	H	W		
10 1/2	13 1/4	10 5/8	8	6	4YC44	5AE70
10 1/2	13 1/4	10 5/8	8	6	4YC44	5AE71
11 1/2	14	11 7/8	8	8	4YC44	5AE72
11 1/2	14	11 7/8	8	8	4YC44	5AE73
11 1/2	14	11 7/8	8	8	4YC44	5AE74
14 1/2	18	14 3/8	8	8	4YC46	5AE75
11 5/8	23 5/8	11 5/8	8	19 1/2	4YC46	5AE76
14 1/2	18	14 3/8	8	10	4YC46	5AE77
14 1/2	23 3/4	14 3/8	8	18 3/4	4YC46	5AE78
14 1/2	23 3/4	14 3/8	8	18 3/4	4YC45	5AE79
14 1/2	23 3/4	14 3/8	8	18 3/4	4YC45	5AE80
14 1/2	23 3/4	14 3/8	8	18 3/4	4YC45	5AE81



5AE68

Low profile ceiling ventilator. Galvanized housing for use with general ventilation applications.



5AE76

Insulated ceiling ventilator. Galvanized housing for use with general ventilation applications.

The products listed above are only a small representation of our full product line. For a complete selection of Dayton HVAC products, see the Grainger catalog or visit grainger.com/dayton

Dayton®