

Compact Fluorescent Lighting



Exclusively from Grainger.

Self-Ballasted Compact Fluorescent Lamps

Provide flicker-free instant starts (less than one second), in temperatures as low as -22 degrees F (-23 degrees C). 82 CRI. Best performance is achieved if operated base up and at 77 degree F ambient temperature. Use only indoors on 120V, 60 Hz circuits. Energy Star compliant.

LAMP SHAPE	LAMP DESIGNATION	LAMP WATTS	INCANDESCENT WATTAGE EQUIVALENT	SPECIAL FEATURES	LAMP TONE	RATED AVERAGE LIFE (HRS.)	ITEM NO.
Spiral T2 1/4" Diameter							
Spiral	7CFL/27	7	25	–	Warm White	10,000	2CUR9
Spiral	7CFL/41	7	25	–	Cool White	10,000	2CUT1
Spiral	11CFL/27	11	40	–	Warm White	10,000	2CUT2
Spiral	11CFL/41	11	40	–	Cool White	10,000	2CUT3
Spiral	13CFL/27	13	60	–	Warm White	10,000	2CUT4
Spiral	13CFL/41	13	60	–	Cool White	10,000	2CUT5
Spiral	13CFL/GU24/27	13	60	GU24 Base	Warm White	10,000	2CUW2
Spiral	13CFL/GU24/41	13	60	GU24 Base	Cool White	10,000	2CUW3
Spiral	20CFL/27	20	75	–	Warm White	10,000	2CUT6
Spiral	20CFL41	20	75	–	Cool White	10,000	2CUT7
Spiral	20CFL/DAY/65	20	75	–	Daylight	10,000	2CUT8
Spiral	23CFL/27	23	100	–	Warm White	10,000	2CUT9
Spiral	23CFL/41	23	100	–	Cool White	10,000	2CUU1
Spiral	20CFL/DAY/65	23	100	–	Daylight	10,000	2CUU2
Spiral T3 3/8" Diameter							
Spiral	20CFL/DIM/27	20	75	Dimmable	Warm White	10,000	2CUU8
Spiral	23CFL/GU24/27	23	100	GU24 Base	Warm White	10,000	2CUW4
Spiral	23CFL/GU24/41	23	100	GU24 Base	Cool White	10,000	2CUW5
Spiral	15CFL/DIM/27	15	60	Dimmable	Warm White	10,000	2CUU7
Spiral	12/20/26CFL/3-Way/27	12/20/26	30/70/100	3-Way	Warm White	10,000	2CUU9
Spiral	40CFL/27	40	125	–	Warm White	6000	2CUU3
Spiral	40CFL/41	40	125	–	Cool White	6000	2CUU4
Spiral	55CFL/27	55	150	–	Warm White	10,000	2CUU5
Biax							
Triple	15CFLT/27	15	60	–	Warm White	10,000	2CUV1
Triple	20CFLT/27	20	75	–	Warm White	10,000	2CUV2
Triple	23CFL/27	23	75	–	Warm White	10,000	2CUV3
Reflectors							
R20	11CFLR20/F/27	11	30	–	Frost	10,000	2CUV4
R30	15CFLR30/F/27	15	65	–	Clear	6000	2CUV5
R30	15CFLR30/DIM/27	15	65	Dimmable	Frost	10,000	2CUV6
PAR30	15CFLPAR30/LN/27 (4)	15	60	Wet Location	Clear	10,000	2CUV7
PAR38	23CFLPAR38/27 (4)	23	90	Wet Location	Clear	10,000	2CUV8
R40	23CFLR40/F/27	23	90	–	Frost	10,000	2CUV9

Use in any direction – base up, base down, or horizontal. Provide up to 70% less energy and last up to 20 times longer than incandescent lamps. Not for use on electronic timers or photocells.



2CUU1



2CUU9



2CUV1

Industrial Products. Quality Brands. Exclusively from Grainger.

For more info and a complete listing of LumaPro products just call, fax, go online to www.grainger.com/lumapro or stop by your local Grainger branch.