

# Shining a Spotlight on our Complete LumaPro® Assortment

CATEGORY		RANGE OF PRODUCTS
<b>Compact Fluorescent Lamps</b>		<b>Plug-In:</b> Single Biac, Double Biac, Triple Biac, 2D Shape; <b>Spiral:</b> T2, T3, T4, T5, Reflector, Globe
<b>Linear Fluorescent 6-Pack Lamps</b>		High Output, T5, T8
<b>LED Lamps</b>		Indicator Lamps, JDR, Miniature, MR11, MR16, PAR16
<b>HID Lamps</b>		High Pressure Sodium, Mercury Vapor, Metal Halide
<b>Incandescent Lamps</b>		A19, A15, BR30, BR40, Halogen Flood, Miniature, MR11, MR16, P25, PAR16, PAR20, PAR30, PAR30L, PAR38, R20, R40, R52, S6, S11, S14, T2 1/2, T3, T4, T4 1/2, T6, T6 1/2, T7, T8, T10, T14
<b>Ballasts</b>		<b>Electronic Fluorescent:</b> High Output, Instant-Start, Programmed Start, Rapid Start, Circline; HID Core and Coil Kits; Ignitors; <b>Magnetic Fluorescent:</b> High Output, Instant Start, Preheat, Rapid Start
<b>Indoor Fluorescent Fixtures</b>		Decorative, High Bay, Low Bay, Striplights, Undercabinet, Wall Brackets
<b>Indoor Incandescent Fixtures</b>		Decorative Bath & Vanity, Recessed Can Lighting, Track Lighting



Exclusively from Grainger.

CATEGORY		RANGE OF PRODUCTS
<b>Induction Lighting</b>		Ceiling Light, Floodlight, Garage, High Bay, Low Bay, Rough Service, Wall Pack
<b>Outdoor Lighting Fixtures</b>		Floodlights, Lampholders, Motion Sensor Lights, Security, Wall Packs,
<b>Vandal-Resistant Fixtures</b>		Incandescent
<b>Task Lighting</b>		<b>Task Lights:</b> Incandescent, Fluorescent; <b>Machine Tool Lights:</b> Incandescent, Fluorescent, Metal Halide
<b>Magnifiers</b>		Round View, Wide Angle/Stadium View
<b>Dock Lights</b>		Incandescent, Quartz Halogen
<b>Portable/ Jobsite Lighting</b>		Cord Reels, Hand Lamps, Jobsite, Mobile Worklights, Portable, String, Utility Tripods

For a full listing of LumaPro products, visit [grainger.com/lumapro](http://grainger.com/lumapro)

**Can't find it? Just ask.** Contact us online or by phone—24/7. We make it easy to find the product you need.



Exclusively from Grainger.