



STC-7003



STC-7002



STC-7001



5S-c



HDST-12

Taking Care Of Business.

Scitec business-class telephones are designed and engineered to meet small office/home office (SOHO), small/medium business (SMB), and Enterprise applications. Choose single-line feature phone, speakerphone, and Caller ID speakerphone models.

Models

Single-line telephones

- STC-7001 feature phone - 10 memory keys
- STC-7002 speakerphone - 10 memory keys
- STC-7003 Caller ID speakerphone - 9 memory keys
- 5S-c Caller ID speakerphone- 5 memory keys
- HDST-12 headset-ready speakerphone - 12 memory keys

Features

- Flash, Hold, Redial, Redial/Pause, Store, Speaker, Mute, Headset, Pause, Dial, and Delete keys on selected models
- Dual NEON/LED message waiting light (7001/7002/HDST-12)
- NEON/LED/Centrex FSK message waiting light (7003/5S-c)
- Voice mail retrieval light, key, or lightbar
- 12, 10, 9, or 5 programmable feature keys
- 2 Year Warranty

Colors

- Grey
- Black

STC-7001 • STC-7002 • STC-7003 • 5S-c • HDST-12

Features & Specifications:

Product Identification & Order Numbers:

- Model No. STC-7003 - 9 Memory Keys
3CZC6 - Grey / 3CZC5 - Black
- Model No. STC-7002 - 10 Memory Keys
3CZC4 - Grey / 3CZC3 - Black
- Model No. STC-7001 - 10 Memory Keys
3CZC2 - Grey / 3CZC1 - Black
- Model No. 5S-c - 5 Memory Keys
3CZC8 - Grey / 3CZC7 - Black
- Model No. HDST-12 - 12 Memory Keys
3CZA8 - Grey / 3CZA9 - Black

Product Information:

- Installation Includes
 - RJ11 Line Cords - 14ft./4.27m
 - Handset Coil Cord - 12ft/3.65m
 - Optional Wall Mount Bracket (not included)
- Line, MW, and Ringer Specifications
 - Line Voltage - Auto-Detect
 - Line Current 20mA-100mA
 - Auto-Detect for 90VDC Neon or Low Voltage
 - LED Applications
 - Ringer Equivalence - 0.6B
- Unit Dimensions
 - 11.0"(l) x 8.75"(w) x 3.0"(h) - 7001/7002/7003
 - 11.0"(l) x 8.75"(w) x 3.0"(h) - 5S-c
 - 11.0"(l) x 8.75"(w) x 3.0"(h) - HDST-12
- Packaging Weight
 - MasterPack Quantities of 12 Units, 48lbs/21.77kg (5S-c)
 - MasterPack Quantities of 12 Units, 36lbs/16.32kg (7001/7002/7003/HDST-12)
- Certifications
 - FCC Part 68, FCC Part 15 & UL 1459 Ref.
 - ADA/FCC Hearing Aid Compliant

Deluxe Features:

- Single Line Speakerphone (7002)
- Single Line Caller ID Speakerphone (7003)
- Headset On/Off Key (HDST-12)
- Volume Control Key (HDST-12)
- Volume Control Toggle Key (7001/7002/7003/5S-c)
- Compatible with PABX Systems
- Soft Key Technology
- Convenient Data Port
- On-Hook Pre-Dialing on Memory Keys
- Industrial Grade Construction with Matte Finish Design
- Non-Slip Base

Audio/Visual Features:

- Telephone Line Powered
- Type I/II Call Waiting Caller ID LCD Screen (7003/5S-c)
- NEON/LED Message Waiting Light: (7001/7002/HDST-12)
- NEON/LED/Centrex FSK Message Waiting Light: (7003/5S-c)
- Voice Mail Retrieval: Programmable lightbar speed dials user directly to voice mail (5S-c)
- 4 Step Speaker and Handset Volume Control
- High/Low/Off Ringer Volume Switch
- Hold Key with LED On/Off Indication
- HAC-Compatible Handset
- ADA-Compliant Volume Control

Programming Features:

- Voice Mail Retrieval Lightbar (5S-c)
- Message Key (HDST-12)
- 12, 10, 9, or 5 Feature Keys with Secure Programming
- Memory Key Entry - Maximum 32 Digits
- Flash Key (all)
- Redial/Pause Key (7001/7002)
- Pause Key (all)
- Store Key (7001/7002/7003/HDST-12)
- Dial Key (7003/5S-c)
- Delete Key 7003/5S-c)
- Set Key (7003)



Wall Mount Bracket Kit with 5' line cord sold separately.

For more information, please contact your Grainger representative.

AVAILABLE THROUGH

GRAINGER®

FOR THE ONES WHO GET IT DONE