












Your Complete Source for Test Instruments

CATEGORY	RANGE OF PRODUCTS	BRANDS	APPLICATIONS	
Infrared Cameras		Both Fixed and Articulating Lens Models	FLIR, Fluke	Industrial and building diagnostic applications commonly used in predictive maintenance programs
Infrared Thermometers		Spot IR Temperature Meters from close focus to long range	Cooper, Extech, Fluke, Westward	Allows for quick and safe temperature measurements suits many applications in electrical and HVAC troubleshooting
Thermocouple Thermometers		Single, Dual and Triple Input Thermometers	Extech, Fluke	Highly accurate temperature measurements for use in HVAC and manufacturing operations
Anemometers		Vane and Hot Wire Anemometers	Dwyer, Extech	Measure air temperature and velocity in HVAC building systems
Balometers		Single, Three, and Five hood Models can measure from 0 to 2500 CFM	TSI Alnor	Used in balancing ventilation systems air flow in industrial commercial buildings
Air Quality Meters		Multifunction air analyzers measure a wide range of factors to determine the air quality	Bacharach, Fluke, TSI Alnor	Measures CO, CO ₂ , humidity, dew point and wet bulb
Gas Leak Detectors		Detects natural gas, acetylene alcohol, ether and other gases	TIF	Identify the presence and source of combustible gases
Tachometers / Stroboscopes		Contact and Non-contact Tachometers and Stroboscopes	Extech, Monarch	Use tachometers to measure speed; stroboscopes perform stop motion inspections on fast moving machines
Force Measurement		Measure Tension, Compression or Torque	Extech	Quality assesment in manufacturing and data acquisition
Moisture Measurement		Pinned and Pinnless Meters	Extech	Building remediation and construction

CATEGORY		RANGE OF PRODUCTS	BRANDS	APPLICATIONS
Water Quality & Soil Instrumentation		Handheld Field Testers, Benchtop Analyzers and Chemical Reagents	Extech, Hanna, YSI	Wastewater treatment, natural resources management, manufacturing and power generation
Static Grounding & Protection		Wrist Straps, Heel Plates, Bench Mats, Antistatic Bags		Electronic service and manufacturing
Bench Meters		Osilloscopes, Function Generators, Power Supplies, Isolation Transformers	Agilent Technologies, BK Precision	Electronic service and manufacturing
Buried Line Locators		Underground Utility Locators and Circuit Tracers	Ridgid	Locate buried water, sewer and electrical service lines. Trace circuits inside industrial and commercial buildings
Multimeters		From Basic Multimeters to Meters with Built-in Datalogging and Thermometers	Amprobe, Extech, Fluke	Measure voltage, continuity, current and temperature
Clamp Meters		AC only to AC/DC TRMS Meters with Built-in Thermometers	Amprobe, Extech, Fluke, Ideal	Measure voltage, continuity, current and temperature
Pressure Gauges		Steel, Plastic and Stainless Steel accuracies up to 0.25%		Measure pressure in shop air systems, hydraulic systems, on equipment and in HVAC building systems
Process Thermometers		Measure Temperatures up to 550°F in a wide range of configurations		HVAC building systems and in many industrial processes
Panel Meters		Measures Voltage, Current and Elapsed Time		Measures voltage, current and elapsed time in many industrial applications
Sound Level Meters		Measure sound levels or frequencies	Extech, Simpson	Used to measure noise levels and properly apply hearing protection
Light Meters		Measures light in Lux and foot-candles	Extech	Measures light output in MRO applications

For a full listing of test instruments products, visit Grainger.com®

Can't find it? Just ask. Contact us online or by phone—24/7. We make it easy to find the product you need.